




# **HEADPHONE AMPLIFIER**

4 Outputs



Description

Headphone signal amplifier with up to 4 headphone outputs with level control each output.

2 output amplifier drawing

Excessive volume can damage your ears or headphones. Before you start using the device, please, turn down the volume to the minimum level O (the knob toward the left). Make sure you use an appropriate volume for listening.







# Tech Data

# **HEADPHONE AMPLIFIER**

4 Outputs

Tech Specification Line Input		
Connector	Impedance	Max. Input level
Jack TS 1/4'', STEREO	100 KΩ	+ 15 dBu
Headphone Outputs		
Connector	Impedance	Max. Output level
Jack TS ¼'', STEREO	80 Q	Aprox. 40 mW en 100 Ω
Power		

<b>Physical Charact</b>	eristics: depend on the format
( honco tormat	MF portable format (see dimensions)
	Rack mount format ( see dimensions )





## Tech Data

# **HEADPHONE AMPLIFIER**

4 Outputs

## Measurements

All tests are performed with calibrated tools according to (ISO 9001:2000/ISO 14001) Audio measurements are done with **Audio Precision APx515 analyser**.

ALL PRODUCTS ON THE WEBSITE OF PINANSON: <u>http://www.pinanson.com/catalogue/en/</u>

SEE OUR GLOSSARY:

http://www.pinanson.com/en/glosario/



Web: <u>www.pinanson.com</u> @:pinanson@pinanson.com

PINANSON S.L Avda. Constitucion, 40. Mondejar (Guadalajara). SPAIN. Telephone: +34 949 385 444 · Fax: +34 949 385 643

### Review: March 2015

For possible changes due to continuous product improvements; Pinanson S.L. reserves the right to change the showed data in this document without notice. The data presented here correspond to the time it was compiled.

